

# ReSound LiNX Quattro™



Call  
Absolute Hearing Solutions  
For Hearing Aid Deals  
614-452-4280

[www.absolutehearingsolutions.com](http://www.absolutehearingsolutions.com)



## Product Description


Based on our most advanced chip platform, the ReSound LiNX Quattro hearing aids features an extended bandwidth of up to 9.5 kHz and a higher input dynamic range of up to 116 dB SPL. Combined with our renowned ReSound audiological heritage, including Binaural Directionality III and Spatial Sense, the solution provides more of the finer sound details for a clearer, fuller and richer sound experience.

ReSound LiNX Quattro is a 6th generation, 2.4 GHz wireless hearing aid that offers direct audio streaming from iOS and Android™\* devices. With ReSound Assist and the ReSound Smart 3D™ app, you can provide remote fine-tuning services for your clients.

The Behind-the-Ear (BTE) model 67 hearing aid is available with a thin tube and a hook, it comes with telecoil functionality as standard, and it works with the full line of ReSound wireless accessories.

ReSound LiNX Quattro BTE hearing aids are iSolate™ nanotech-coated for optimum durability and meet the IP68 classification for ingress protection.

\*Compatible from Android version 10 and Bluetooth® 5.0 with the Android streaming to hearing aids feature.




Model	RE967-DWT	RE767-DWT	RE567-DWT
<b>Device Configurations</b>			
Battery size	312		
Colors available	17		
<b>Audiological Features</b>			
WARP compression (WDRC) - number of channels	17	14	12
Binaural Directionality III	●	-	-
Spatial Sense	●	-	-
Binaural Directionality	-	●	-
Natural Directionality II	●	●	●
Directional Mix Processor	●	●	●
Adjustable directional mix	●	-	-
Synchronized Soft Switching	●	●	-
Soft Switching	●	●	●
Autoscope Adaptive Directionality	●	-	-
Multiscope Adaptive Directionality	-	●	-
Adaptive Directionality	-	-	●
Binaural Environmental Optimizer II	●	-	-
Environmental Optimizer	-	●	-
Noise Tracker II	●	⊙	○
Expansion	●	⊙	○
Impulse Noise Reduction	●	●	-
Wind Guard	●	⊙	○
Sound Shaper	●	●	●
DFS Ultra II	●	●	●
Music Mode	●	●	●
Synchronized Acceptance Manager	●	●	●
Tinnitus Sound Generator	●	●	●
<b>Functional Features</b>			
Synchronized Push Button*	●	●	●
Smart Start	●	●	●
Phone Now	●	●	●
Comfort Phone	●	●	●
Ear to Ear Communication	●	●	●
Direct audio streaming	●	●	●
ReSound TV Streamer 2, Remote Control, Remote Control 2, Phone Clip+, Micro Mic and Multi Mic	●	●	●
ReSound Smart 3D™ app	●	●	●
<b>ReSound Assist</b>			
Remote Fine Tuning	●	●	●
Remote Firmware Updates	●	●	●
<b>Fitting Features</b>			
ReSound Smart Fit™ 1.6 or higher	●	●	●
Fully Flexible Programs	4	4	4
Auto DFS	●	●	●
Onboard Analyzer II	●	●	●
Wireless Fitting with Noalink Wireless	●	●	●

○ Basic

● Advanced

● Ultimate

\* Also including functionality for synchronized Push Button Volume Control



© 2019 GN Hearing A/S. All rights reserved. ReSound is a trademark of GN Hearing A/S. Apple, the Apple logo, iPhone, iPad and iPod touch are trademarks of Apple Inc., registered in the US and other countries. Android is a trademark of Google LLC. The Bluetooth word mark and logos are registered trademarks owned by Bluetooth SIG, Inc.



**Absolute Hearing Solutions LLC**

[absolutehearing@att.net](mailto:absolutehearing@att.net)

750 Cross Pointe Road Suite F  
Gahanna, Ohio 43230

Phone: 614-452-4280  
Toll Free: 888-803-2159  
Fax: 614-577-0481

[www.absolutehearingsolutions.com](http://www.absolutehearingsolutions.com)

401236011US CA VA-20.03-Rev.C

Manufacturer according to FDA:

GN ReSound North America  
8001 E Bloomington Freeway  
Bloomington, MN 55420  
USA  
1-888-735-4327  
resound.com

Manufacturer according to FDA:

ReSound Government Services  
8001 E Bloomington Freeway  
Bloomington, MN 55420  
USA  
1-800-392-9932  
resound.com/veterans

Manufacturer according to Health Canada:

ReSound Canada  
2 East Beaver Creek Road, Building 3  
Richmond Hill, ON L4B 2N3  
Canada  
1-888-737-6863  
resound.com

# Technical specifications

		RE67-DWT (Thin tube)		
		IEC 60118-0 2nd IEC 711 Ear Simulator	IEC 60118-0 3rd IEC 60118-7 ANSI S3.22 2cc coupler	
Reference test gain (60 dB SPL input)	1600 Hz/HFA	41	36	dB
Full-on gain (50 dB SPL input)	Max. 1600 Hz/HFA	60 52	52 47	dB
Maximum output (90 dB SPL input)	Max. 1600 Hz/HFA	127 117	123 113	dB SPL
Total harmonic distortion	500 Hz	0.5	0.4	%
	800 Hz	0.2	0.1	
	1600 Hz	0.6	0.4	
	3200 Hz	-	0.2	
Telecoil sensitivity (1 mA/m input)	Max.	91	81	dB SPL
HFA - SPLIV @ 31.6 mA/m (ANSI)	HFA	104	96	
Full-on telecoil sensitivity @ 1mA/m	1600 Hz/HFA	82	77	
Equivalent input noise, w/o noise reduction		26	22	dB SPL
1/3 Octave Equivalent input noise, w/o noise reduction		10	10	dB SPL
Frequency range IEC 60118-0: 2015		100-9260*	100-7800	Hz
Current Drain (Quiescent/Operating)		1.17/1.24	1.17/1.22	mA

Data in accordance with IEC60118-0:2015-06, IEC60118-7 and ANSI S3.22-2009, supply Voltage 1.3V

\* Measured according to IEC60118-0:2015, with 711 Ear Simulator coupler.


# Technical specifications

		RE67-DWT (Closed)		
		IEC 60118-0 2nd IEC 711 Ear Simulator	IEC 60118-0 3rd IEC 60118-7 ANSI S3.22 2cc coupler	
Reference test gain (60 dB SPL input)	1600 Hz/HFA	44	39	dB
Full-on gain (50 dB SPL input)	Max. 1600 Hz/HFA	65 55	56 49	dB
Maximum output (90 dB SPL input)	Max. 1600 Hz/HFA	130 123	121 116	dB SPL
Total harmonic distortion	500 Hz	0.8	0.7	%
	800 Hz	0.9	0.6	
	1600 Hz	0.6	0.6	
	3200 Hz	-	0.1	
Telecoil sensitivity (1 mA/m input)	Max.	95	85	dB SPL
HFA - SPLIV @ 31.6 mA/m (ANSI)	HFA	105	99	
Full-on telecoil sensitivity @ 1mA/m	1600 Hz/HFA	85	79	
Equivalent input noise, w/o noise reduction		26	23	dB SPL
1/3 Octave Equivalent input noise, w/o noise reduction		10	10	dB SPL
Frequency range IEC 60118-0: 2015		100-8060*	100-6800	Hz
Current Drain (Quiescent/Operating)		1.17/1.24	1.18/1.34	mA


Data in accordance with IEC60118-0:2015-06, IEC60118-7 and ANSI S3.22-2009, supply Voltage 1.3V

\* Measured according to IEC60118-0:2015, with 711 Ear Simulator coupler.


IEC 60118-0: 1983\_AMD1:1994  
IEC 711 Ear Simulator




ANSI S3.22-2014  
IEC 60118-0:2015  
JIS C 5512: 2015  
2cc coupler



IEC 60118-0: 1983\_AMD1:1994  
IEC 711 Ear Simulator




ANSI S3.22-2014  
IEC 60118-0:2015  
JIS C 5512: 2015  
2cc coupler




Patents pending

Patents pending


Full-On and Reference Test Gain




Full-On and Reference Test Gain



Full-On and Reference Test Gain




Full-On and Reference Test Gain



All specifications are subject to change without notice

All specifications are subject to change without notice

Full-On Telecoil Response  
Input level 10 mA/m



Full-On Telecoil Response  
Input level 10 mA/m

